



Cellcore 200mm HG 40/50		
Panel Depth	Max. Clear Void	Beam Depth
200mm	100mm	0-1540mm
Cellcore HX S, HX B & HX Plus options are available upon request		

**Standard Detail**



Tel : 01403 799600  
 Email : techsupport@cordek.com

Drg. Title:  
 Standard Ground Beam Detail :  
 Cellcore HG - Medium Heave Potential

Drawn: SJP

Date: June.2017	Scale: NTS	Rev. - 002
-----------------	------------	------------

Drg No.ENG/GH/CELL/200 HG 40/50/GBEAM

**Products :-**

Cellcore 200mm HG 40/50.  
 Heaveguard 50mm.

**Notes :-**

- The appropriate specification of Cellcore and Heaveguard panels should be selected based upon the information provided in the relevant Cordek technical guidance.
- Cellcore panels should be installed on a smooth, flat, well compacted surface comprising of a sand / cement or concrete blinding.
- Where necessary, joints between individual Cellcore panels should be sealed using Cordek formwork tape.
- Care should be taken not to surcharge the Cellcore panels with either reinforcement or concrete.