



| Cellcore 300mm HG 40/50 | | |
|--|-----------------|------------|
| Panel Depth | Max. Clear Void | Beam Depth |
| 300mm | 150mm | 0-1540mm |
| Cellcore HX S, HX B & HX Plus options are available upon request | | |

Standard Detail



Tel : 01403 799600
 Email : techsupport@cordek.com

Drg. Title:
 Standard Ground Beam Detail :
 Cellcore HG - High Heave Potential

Drawn: SJP

Date: June.2017 Scale: NTS Rev. - 002

Drg No.ENG/GH/CELL/300 HG 40/50/GBEAM

Products :-

Cellcore 300mm HG 40/50.
 Heaveguard 75mm.

Notes :-

- The appropriate specification of Cellcore and Heaveguard panels should be selected based upon the information provided in the relevant Cordek technical guidance.
- Cellcore panels should be installed on a smooth, flat, well compacted surface comprising of a sand / cement or concrete blinding.
- Where necessary, joints between individual Cellcore panels should be sealed using Cordek formwork tape.
- Care should be taken not to surcharge the Cellcore panels with either reinforcement or concrete.